

Gimbal expansion joint DN 6"

Oper. pressure [bar]: 4.1

Oper. temp. range [K]: 490 ÷ 540

Oper. travel ranges (max.)
- angular [°] : ± 5

Weight (max) [Kg] : 1.8

Spring rates (max.)
- angular [N m/°] : 1.94

Operating fluids : air

Bellows material : Ti 40

Application : AIRBUS bleed air ducts

Status : Qualified for flight

